

MoonBeam[™]3 Disinfection Technology

On-Demand Targeted Disinfection System

MoonBeam 3 delivers powerful UVC light to provide fast, on-demand broad area disinfection of high-touch surfaces in as little as 90 seconds.

Features

- Three individually adjustable articulating heads, each generating a broad umbrella of intense UVC light
- Base unit locking casters allow easy movement and positioning anywhere. UVC heads unfold for positioning in seconds
- Remote cover controls operation and acts as a sensor during disinfection to ensure safety. Cover also protects light heads and enables convenient transport from room to room. Optional multi-access point motion sensor also available

Benefits

- Cost-effective operation low operating cost and minimal maintenance
- Complete disinfection effective against contamination from surface areas accidentally missed in cleaning
- Ideal solution for frequently-touched, hard-to-clean surfaces and intricate, hard-to-wipe equipment
- Fume-free, chemical-free disinfection

Application

Suited for high-touch surfaces such as the entire patient bed area, operating rooms, bathrooms and fixtures, keyboards, monitors, and work stations on wheels (WOWs).





MoonBeam[®]3 Disinfection Technology

On-Demand Targeted Disinfection System

Product Specifications			
Description	MoonBeam™3	Description	MoonBeam™3
UVC vertical dosing height range:	6" (15 cm) to 84" (210 cm) high	Chemical Usage:	None
		Device Size:	15" x 44" (38 cm x 112 cm)
Cycle time in seconds:	90, 180, 300, 600		
Device weight:	39 lbs. (17 kg) complete base unit: 27 lbs. (13 kg)	Acoustic Noise:	Negligible
		Power:	100-120V~, 3.2A, 50/60Hz 200-240V~, 1.6A, 50/60Hz
Environmental:	No ozone generation, high output UVC lamps		

MoonBeam™3 Device Components			
Product Code	Description	Details	
DMOONBEAM3	MoonBeam™3 UVC Disinfection Technology Device	MoonBeam™3 is designed for fast, on-demand disinfection of high-touch surfaces in patient areas	
DMOON3SENTRY	MoonBeam™3 Sentry Assist Technology	For added safety this system is designed to be placed in a location physically separated from the MoonBeam™3 base and provides full zone motion detection for a higher level of personnel detection safety	
DMOON3UVCBULBS	MoonBeam™3 Bulb Set (3 bulbs)	3-UVC Replacement Bulbs for MoonBeam™3	